



Gas Analysis

Sample Gas Filter AGF-VA-350

Even if the particular contaminant has already been removed at the extraction point through effective particle filtration inside the gas sampling probe, in long or branched sample gas line there is a risk of secondary contamination. Additional filters are therefore often installed at the point where the sample gas enters the analysis system and also before delicate system components. The filter housings must be made of corrosion-resistant, non-absorbent materials, easy to install and easy to maintain. They should further be compatible with various filter elements.

Model AGF-VA-350 has a small stainless steel housing and is suitable for operating pressures up to 5076 psi.

Very quick and easy filter changes without tools

Low dead volume


Buhler Technologies LLC, 1030 West Hamlin Road, Rochester Hills, MI 48309 Phone: 248.652.1546, Fax: 248.652.1598


Variable wall mounting via mounting bracket

(Auto-) condensate drain option through connection thread (NPT 1/4") inside the filter cover



Dimensions







Use in explosive areas (additional notices):

The filter meets the fundamental safety requirements of Directive 2014/34/EU and is suitable for use in category 2G, explosion group IIC areas. The filter is not marked, as it does not have an innate ignition source, so Directive 2014/34/EU does not apply.

Flammable gases, explosion group IIC, which could occasionally be explosive during normal operation may be conveyed through the filter.

Be sure to observe the relevant operating instructions!

Ambient temperature range when used in Ex areas: 41 °F \leq T_{amb} \leq 140 °F.

Technical Data

Filter

Dead volume with filter element	1.1 cu. in.			
Material - filter housing	1.4404 (SS 316L)			
Material - gasket	Viton FEP shrouded			
Material - filter element	see table			
Weight	approx. 1.76 lb			
Operating pressure max.	5076 psi			
Medium temperature max.	302 °F			

Ordering instructions

Filter (empty housing)

Item no.	Model	Material	permissible explosion group of the external filter area
4135999	AGF-VA-350-T for installing GF filter elements	1.4404 (SS316L), Viton gasket, FEP shrouded	IIC
41359993	Mounting bracket	1.4301 (SS 304)	
9008802	Plug NPT 1/4	1.4401 (SS 316)	
9009297	O-ring	Viton/FEP shrouded	

Filter elements

Item no.	Model	Material	Filter fineness	max. temperature	Packaging unit	permissible explosion group of the internal filter area
4135G002	GF2	Fibreglass / epoxy resin	2 μm	302 °F	1 count	IIC
4135G005	GF5	Fibreglass / epoxy resin	5 μm	302 °F	1 count	IIC
4135G010	GF10	Fibreglass / epoxy resin	10 μm	302 °F	1 count	IIC